

△×				APPROVED	CHECKED	MATERIAL 材料				—		CHAMFER 一般面取		—		QUANTITY 個数	
△×				T. A.	T. A.	TREATMENT 処理				—		FINISHING 仕上		—		—	
△×						TREATMENT CONTACT 処理接点				—		DECENTRATION 偏芯		—			
△×				DESIGNED	DRAWN	~~OVER 250 UP TO 1000 ±0.3 ±0.5 ±1.0 ±0.2~~				UNIT (mm)	ANGLE 角度	METHOD 図法	REMARK 適用 (機種名)				
△× 4	Focus ±3 削除 / 表記変更	19. 03. 03	T. F.			~~OVER 63 UP TO 250 ±0.2 ±0.3 ±0.6 ±0.15~~					—		V S Z - 0 5 3 0				
△× 3	外観変更 (ブルーライン削除×1) (フォーカス目盛変更×1、絞り目盛変更×1)	17. 06. 14	T. T.			~~OVER 16 UP TO 63 ±0.1 ±0.2 ±0.4 ±0.1~~					SCALE	1 / 1	NAME	D R A W I N G / 外 観 図			
NO.×箇所	REVISION 訂正事項	DATE	NAME			~~OVER 0 UP TO 16 ±0.05 ±0.1 ±0.2 ±0.1~~					DATE	' 11. 04. 22	DRAW NO.	0 D M Z 0 0 6 7 A 3			
						TOLERANCES A B C S											